

## Rolling Mill



To prepare sample sheets from PVC granules for quick testing of raw material/finished products in laboratory.

Eliminates need of running extruders on production lines, thus saving precious raw material & production loss.

Electrically heated rollers.

Rolling mill is made of corrosion resistant steel, surface hardened and polished.

High temperature sealings are used for the bearings.

Both rolls run at a fixed speed and with a constant friction ratio.



### **Technical Data**

<b>Roll diameter:</b>	150 mm
<b>Roll width:</b>	300 mm
<b>Working width:</b>	275 mm
<b>Roll Speed:</b>	Approx. 22/27 min-1
<b>Power:</b>	2 * 1.5 kW
<b>Torque:</b>	500 Nm
<b>Roll Temperature:</b>	Up to 220° C